






































































































2022-0038  
05/2023

**R-M – UV lamp overview**

Product	UV - Body filler	UV - Primer filler	UV – Clear coat
<b>IRT UVA 1 PREPCURE 3 (395nm)</b>	 100 cm x 100cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT UVA 1 PREPCURE 4 (395nm)</b>	 100 cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT UVA 2 PREPCURE 4 (395nm)</b>	 100 cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT COMBI 4-1 IR-UVA (395nm)</b>	 100 cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT COMBI 4-2 IR-UVA (395nm)</b>	 100cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT COMBI 4-10 IR-UVA (395nm)</b>	 100 cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min









2022-0038  
05/2023

<b>IRT COMBI 4-20 IR-UVA (395nm)</b>	 100 cm x 100 cm  55 cm  5 min	 100 cm x 100 cm  55 cm  5 min	 20 cm x 30 cm  20 - 30 cm  5 min
<b>IRT SpotCure (LED - 395nm)</b>	 10 cm  10 cm  2 min	 10 cm  10 cm  2 min	
<b>IRT SpotCure2 (LED - 395nm)</b>	 15 cm x 30 cm  10 cm  1 min 30 sec	 15 cm x 30 cm  10 cm  1 min	
<b>IRT Smart Cure (LED - 395nm)</b>	 10 cm  10 cm  2 min 30 sec	 10 cm  10 cm  2 min	
<b>SpectrateK Instacure UVLED (LED - 395nm)</b>	 10 cm  10 cm  3 min	 10 cm  10 cm  3 min	
<b>TESLA Cure R100 (LED - 395nm)</b>	 10 cm  10 cm  3 min	 10 cm  10 cm  2 min	
<b>Scangrip UV gun (LED - 395nm)</b>	 10 cm  10 cm  3 min	 10 cm  10 cm  2 min	



2022-0038  
05/2023

<b>Scangrip NOVA-UV S (LED - 390nm)</b>	 10 cm	 10 cm	
	 10 cm	 10 cm	
	 3 min	 2 min	