






































































































2022-0038
05/2023

RM – Aperçu des lampes UV

Produit Lampe UV	Mastic UV	Impression-apprêt UV	Vernis UV
IRT UVA 1 PREPCURE 3 (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
IRT UVA 1 PREPCURE 4 (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
IRT UVA 2 PREPCURE 4 (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
IRT COMBI 4-1 IR-UVA (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
IRT COMBI 4-2 IR-UVA (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
IRT COMBI 4-10 IR-UVA (395nm)	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes









2022-0038
05/2023

<p>IRT COMBI 4-20 IR-UVA (395nm)</p>	 100 cm x 100 cm  55cm  5 minutes	 100 cm x 100 cm  55cm  5 minutes	 20 cm x 30 cm  20 - 30 cm  5 minutes
<p>IRT SpotCure (DEL - 395nm)</p>	 10 cm  10 cm  2 minutes	 10 cm  10 cm  2 minutes	
<p>IRT SpotCure2 (DEL - 395nm)</p>	 15 cm x 30 cm  10 cm  1 min 30 s	 15 cm x 30 cm  10 cm  1 minute	
<p>IRT Smart Cure (DEL - 395nm)</p>	 10 cm  10 cm  2 min 30 s	 10 cm  10 cm  2 minutes	
<p>SpectrateK Instacure UVLED (LED - 395nm)</p>	 10 cm  10 cm  3 minutes	 10 cm  10 cm  3 minutes	
<p>TESLA Cure R100 (DEL - 395nm)</p>	 10 cm  10 cm  3 minutes	 10 cm  10 cm  2 minutes	
<p>Pistolet UV Scangrip (LED - 395nm)</p>	 10 cm  10 cm  3 minutes	 10 cm  10 cm  2 minutes	



2022-0038
05/2023

Scangrip NOVA-UV S (LED - 390nm)	 10 cm	 10 cm	
	 10 cm	 10 cm	
	 3 minutes	 2 minutes	